
IXYS

HiPerFET™ Power MOSFETs

IXFX 100N25
IXFK 100N25


V_{DSS} = 250 V
I_{D25} = 100 A
$R_{DS(on)}$ = 27 mΩ
$t_{rr} \leq$ 250 ns

Single MOSFET Die




Symbol	Test Conditions	Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C	250	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ	250	V
V_{GS}	Continuous	±20	V
V_{GSM}	Transient	±30	V
I_{D25}	T_C = 25°C (MOSFET chip capability)	100	A
I_{D104}	T_C = 104°C (External lead capability)	75	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	400	A
I_{AR}	T_C = 25°C	100	A
E_{AR}	T_C = 25°C	64	mJ
E_{AS}	T_C = 25°C	3	J
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/µs, $V_{DD} \leq V_{DSS}$ $T_J \leq$ 150°C, R_G = 2 Ω	5	V/ns
P_D	T_C = 25°C	560	W
T_J		-55 ... +150	°C
T_{JM}		150	°C
T_{stg}		-55 ... +150	°C
T_L	1.6 mm (0.063 in.) from case for 10 s	300	°C
M_d	Mounting torque TO-264	0.9/6	Nm/lb.in.
Weight	PLUS 247	6	g
	TO-264	10	g

PLUS 247™ (IXFX)



TO-264 AA (IXFK)



G = Gate D = Drain
S = Source TAB = Drain

Features
- International standard packages
- Low $R_{DS\ (on)}$ HDMOS™ process
- Rugged polysilicon gate cell structure
- Unclamped Inductive Switching (UIS) rated
- Low package inductance
  - easy to drive and to protect
- Fast intrinsic rectifier

Applications
- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- AC motor control
- Temperature and lighting controls

Advantages
- PLUS 247™ package for clip or spring mounting
- Space savings
- High power density

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.
V_{DSS}	V_{GS} = 0 V, I_D = 3mA	250		V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 8mA	2.0		4.0 V
I_{GSS}	V_{GS} = ±20 V, V_{DS} = 0			±200 nA
I_{DSS}	$V_{DS} = V_{DSS}$ T_J = 25°C			100 µA
	V_{GS} = 0 V T_J = 125°C			2 mA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 I_{D25} Note 1			27 mΩ

© 2001 IXYS All rights reserved


Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	min.	typ.	max.	
g_{fs}	V_{DS} = 10 V; I_D = 0.5 I_{D25} Note 1	40	70		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		9100		pF
C_{oss}			1800		pF
C_{rss}			600		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25} R_G = 1 Ω (External),		42		ns
t_r			55		ns
$t_{d(off)}$			110		ns
t_f			40		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 V_{DSS}, I_D = 0.5 I_{D25}		300		nC
Q_{gs}			57		nC
Q_{gd}			160		nC
R_{thJC}				0.22	K/W
R_{thCK}			0.15		K/W

Source-Drain Diode

Symbol	Test Conditions (T_J = 25°C, unless otherwise specified)	min.	typ.	max.	
I_S	V_{GS} = 0 V			100	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			400	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Note 1			1.5	V
t_{rr}	I_F = 50A,-di/dt = 100 A/µs, V_R = 100 V			250	ns
Q_{RM}			1.4		µC
I_{RM}			10		A

Note: 1. Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %


PLUS 247™ Outline



Terminals: 1 - Gate
2 - Drain (Collector)
3 - Source (Emitter)
4 - Drain (Collector)

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.83	5.21	.190	.205
A_1	2.29	2.54	.090	.100
A_2	1.91	2.16	.075	.085
b	1.14	1.40	.045	.055
b_1	1.91	2.13	.075	.084
b_2	2.92	3.12	.115	.123
C	0.61	0.80	.024	.031
D	20.80	21.34	.819	.840
E	15.75	16.13	.620	.635
e	5.45 BSC		.215 BSC	
L	19.81	20.32	.780	.800
L1	3.81	4.32	.150	.170
Q	5.59	6.20	.220	0.244
R	4.32	4.83	.170	.190

TO-264 AA Outline



Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	4.82	5.13	.190	.202
A1	2.54	2.89	.100	.114
A2	2.00	2.10	.079	.083
b	1.12	1.42	.044	.056
b1	2.39	2.69	.094	.106
b2	2.90	3.09	.114	.122
c	0.53	0.83	.021	.033
D	25.91	26.16	1.020	1.030
E	19.81	19.96	.780	.786
e	5.46 BSC		.215 BSC	
J	0.00	0.25	.000	.010
K	0.00	0.25	.000	.010
L	20.32	20.83	.800	.820
L1	2.29	2.59	.090	.102
P	3.17	3.66	.125	.144
Q	6.07	6.27	.239	.247
Q1	8.38	8.69	.330	.342
R	3.81	4.32	.150	.170
R1	1.78	2.29	.070	.090
S	6.04	6.30	.238	.248
T	1.57	1.83	.062	.072

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETS and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.