


0.020" $\pm$ 0.002" DIAMETER,
24 AWG, 1.0" LONG MINIMUM,
TINNED CCS



RESISTANCE @ +25°C = 250,000 Ω $\pm$ 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED LIQUID)
 MAXIMUM TEMPERAURE RATING = +300°C

---	ISO RELEASE	11/19/03	DD
"A"	LEAD WIRE DIAMETER WAS 0.020" $\pm$ 0.001"	11/19/03	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 12/07/99

REV "A"

LAYER 0 OF 1

U.S. SENSOR CORP.

1832 W. COLLINS AVE.

ORANGE, CA 92867

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N 254JG1J