




RESISTANCE @ +25°C = 10,000 Ω ± 5%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (+25 TO +85°C) = 3,977°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 TEMPERATURE RATING = -50 TO +300°C

\*\*\* ROHS COMPLIANT \*\*\*

SEE MANUFACTURING SPECIFICATION (LAYER 1)

|      |                       |          |     |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 11/14/13 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |                                                                                                                                            |
|----------|-------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| SCALE    | NONE        | U.S. SENSOR corp.<br>© COPYRIGHT<br>714-639-1000 <a href="http://www.ussensor.com">www.ussensor.com</a><br>NTC GLASS PROBE<br>P/N GL103J5J |
| DRAWN BY | DAN DANKERT |                                                                                                                                            |
| DATE     | 11/14/13    |                                                                                                                                            |
| REV.     | NONE        |                                                                                                                                            |
| LAYER    | 0 OF 2      |                                                                                                                                            |