


RTD ELEMENT RESISTANCE @ 0°C = 1,000 Ω ± 0.12%
RTD ELEMENT ACCURACY @ °C = ± 0.30°C
RTD ELEMENT ACCURACY CLASS = DIN EN 60751 F 0.3 ("B")
TCR = 3,850 ppm/°C
MAXIMUM TEMPERATURE RATING = +105°C

MOUNTING-HOLE DIAMETER = 0.197" NOMINAL
MOUNTING-HOLE STUD-SIZE = #10

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
"A"	CLARIFIED ACCURACY CLASS	06/30/17	DD
NONE	RELEASE TO PRODUCTION	02/05/15	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 02/05/15

REV. "A"

LAYER 0 OF 2

© COPYRIGHT

U.S. SENSOR CORP.

714-639-1000 www.ussensor.com

RTD PROBE ASSY

P/N USW3866