

# 155 SERIES BAYONET IN-LINE FUSE HOLDER



## Features and Benefits

- 19" wire loop for cut-and-wire installation
- Fuse Holder UL Recognized up to 20A at 32V
- Black Thermoset Knob and Body Rated UL94 V-0

## Applications

- In-line mounted 3AG/3AB/SFE Glass Fusing

## Description

155 Series In-line Bayonet Knob Fuse Holders are intended for use at 32V or less for 3AG, 3AB, or SFE style glass fuses. The body and knob features a secure spring-loaded twist lock and are each made of Black Thermoset (UL94 V-10) for flammability resistance. Fuse Holder UL Recognized to 20A, 32V DC.

## Web Resources

Download 2D print and technical resources at:  
[littelfuse.com/155Series](http://littelfuse.com/155Series)

## Specifications Overview

|                               |                    |
|-------------------------------|--------------------|
| <b>Max Voltage:</b>           | 32V DC             |
| <b>Available Fuse Rating:</b> | 3A                 |
| <b>Wire Size:</b>             | 18 AWG             |
| <b>Color:</b>                 | Black              |
| <b>Operating Temp:</b>        | -40° C to + 125° C |

## Recommended Fuses



**SFE Glass Fuses**  
Automotive Glass  
Body Fuses



**3AG and 3AB Fast-Acting Fuse**  
Automotive Glass  
Body Fuses

## Ordering Information

| PART NUMBER  | DESCRIPTION                                      |
|--------------|--|
| 01550500Z-UL | UL In-line Bayonet Knob Fuse Holder with 3A Fuse |



Visit [Littelfuse.com](http://Littelfuse.com) for the most up-to-date product information. Littelfuse products are designed for specific applications and should not be used for any purpose (including, without limitation, automotive applications) not expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse product documentation.