


RESISTANCE @ +77°F (+25°C) = 10,000 Ω NOMINAL
ACCURACY (+65 TO +85°F) (+18.3 TO +29.4°C) = ± 1.0°F (± 0.56°C)
RESISTANCE/TEMPERATURE CURVE = "J"
BETA "β" (+32 TO +122°F) (0 TO +50°C) = 3,892°K NOMINAL
TEMPERATURE COEFFICIENT @ +77°F (+25°C) = −4.4%/°C NOMINAL
MAXIMUM TEMPERATURE RATING = +221°F (+105°C)

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	12/15/09	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE
DRAWN BY	DAN DANKERT
DATE	12/15/09
REV.	NONE
LAYER	0 OF 2

U.S. SENSOR CORP.
1832 W. COLLINS AVE.
ORANGE, CA. 92867
714-639-1000 www.ussensor.com

NTC THERMISTOR PROBE

P/N USP10680