


RESISTANCE @ +25°C = 500,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "R"
TEMPERATURE COEFFICIENT @ +25°C = −4.68%/°C NOMINAL
BETA "β" (0 TO +50°C) = 4,140°K NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +300°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	03/15/04	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 01/20/95

REV. NONE

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N 504RG1K