




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRE: 24 AWG, STRANDED CONDUCTOR,
 TWO CONDUCTOR, PVC INSULATED ZIPCORD

MOISTURE RESISTANT PROBE ASSEMBLY

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	LEAD WIRE LENGTH WAS 12" $\pm$ 1"	09/29/10	DD
NONE	RELEASE TO PRODUCTION	04/02/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR corp. 1832 W. COLL INS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com	
DRAWN BY	DAN DANKERT		
DATE	04/02/10		
REV.	"A"		
LAYER	0 OF 2	TEMPERATURE SENSOR	
		P/N	USP10973