

SE-330HV NEUTRAL-GROUNDING-RESISTOR MONITOR SETTINGS

SE-330HV Model Number: SE-330HV - ____ - ____

SE-330HV Serial Number: _____ Revision: _____

Substation Identification: _____

Transformer Specifications: _____

SE-330 Communications

| CHECK ONE | |
|--------------------------|--------------|
| <input type="checkbox"/> | Local RS-232 |
| <input type="checkbox"/> | Other |

Current Transformer

| CHECK ONE | |
|--------------------------|---|
| <input type="checkbox"/> | EFCT (5-A primary rating when connected to sensitive input) |
| <input type="checkbox"/> | SE-CS30 (30-A primary rating when connected to sensitive input) |
| <input type="checkbox"/> | Other: |

Current Transformer Connection

| CHECK ONE | |
|--------------------------|-----------------------------------|
| <input type="checkbox"/> | Sensitive Input (Terminals 8, 11) |
| <input type="checkbox"/> | 1-A Input (Terminals 9, 11) |
| <input type="checkbox"/> | 5-A Input (Terminals 10, 11) |

Sensing Resistor

| CHECK ONE | |
|--------------------------|----------|
| <input type="checkbox"/> | ER-15KV |
| <input type="checkbox"/> | ER-25KV |
| <input type="checkbox"/> | ER-35KV |
| <input type="checkbox"/> | ER-72 KV |

Remote Indication

| CHECK ONE | |
|--------------------------|--------|
| <input type="checkbox"/> | None |
| <input type="checkbox"/> | RK-232 |
| <input type="checkbox"/> | Other: |

NGR Ratings

Current: _____ A

Voltage: _____

Time: _____

Resistance: _____ Ω

Serial No.: _____

Mfg.: _____

GF Trip Level

Setting: _____ % _____ A

GF Trip Time

Setting: _____ s


VN Trip Level

Setting: _____ V

X 1 for 100 k Ω Sensing Resistor: _____

X 5 for 200 k Ω Sensing Resistor: _____

SE-330HV NEUTRAL-GROUNDING-RESISTOR SETTINGS



CONFIGURATION SWITCH SETTINGS

| | | CHECK ONE | | CHECK ONE |
|-----|------------------|-----------|----------------------|-----------|
| S1: | Spare | | | |
| S2: | Fail-Safe | | Non-Fail-Safe | |
| S3: | Latching GF Trip | | Non-Latching GF Trip | |
| S4: | Latching RF Trip | | Non-Latching RF Trip | |
| S5: | 200 k Ω | | 100 k Ω | |
| S6: | 50 Hz | | 60 Hz | |
| S7: | Spare | | | |
| S8: | Run | | Upgrade | |

System Calibration

Calibration Successful: _____

Date (YYYY-MM-DD): _____

Calibration Number (if available): _____