



产品认证证书

证书编号: CQC16001159721

申请人名称及地址

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 美国

制造商名称及地址

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 美国

生产企业名称及地址

昆山利韬电子有限公司 (V015036)
江苏省昆山综合保税区B区中央大道389号

产品名称和系列、规格、型号

热敏电阻 (限流型)

见附件

产品标准和技术要求

GB8898-2011; GB/T7153-2002; GB14536.1-2008

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471553-2015认证规则的要求, 特发此证。

发证日期: 2016年11月30日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0090406



PRODUCT CERTIFICATE

No.: CQC16001159721

NAME AND ADDRESS OF THE APPLICANT

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 USA

NAME AND ADDRESS OF THE MANUFACTURER

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 USA

NAME AND ADDRESS OF THE FACTORY

Littelfuse Electronics (Kunshan) Co.,Ltd (V015036)
No.389 Central Avenue, B Zone EPZ, Kunshan City, Jiangsu 215301 PRC

NAME, MODEL AND SPECIFICATION

Polyswitch PPTC

See Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB8898-2011;GB/T7153-2002;GB14536.1-2008

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471553-2015.

Date of issue: Nov.30,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:


Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0090406



产品认证证书

附录:

第 1 页 共 3 页

证书编号: CQC16001159721

纸号: 90406

LVR005N(LVR005NK,LVR005NK-2,LVR005NS,LVR005NS-1,LVR005NS-2) (电阻值范围 18.5 Ω -31.0 Ω):

005 表示不动作电流 0.05A; -1 表示拔脚; -2 表示卷装; N 表示新设计; K 表示标准弯脚引线; NS 表示直引线;

LVR008N(LVR008NK,LVR008NK-2,LVR008NS,LVR008NS-1,LVR008NS-2) (电阻值范围 7.4 Ω -12.0 Ω):

008 表示不动作电流 0.08A; -1 表示拔脚; -2 表示卷装; N 表示新的设计; K 表示标准弯脚引线; NS 表示直引线;

LVR012(LVR012K,LVR012K-2,LVR012S,LVR012S-1,LVR012S-2) (电阻值范围 3.0 Ω -6.5 Ω):

012 表示不动作电流 0.12A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

LVR016(LVR016K,LVR016K-2,LVR016S,LVR016S-1,LVR016S-2) (电阻值范围 2.5 Ω -4.1 Ω):

016 表示不动作电流 0.16A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

LVR025(LVR025K,LVR025K-2,LVR025S、LVR025S-1,LVR025S-2) (电阻值范围 1.3 Ω -2.1 Ω):

025 表示不动作电流 0.25A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

LVR033(LVR033K,LVR033K-2,LVR033S,LVR033S-2) (电阻值范围 0.77 Ω -1.24 Ω):

033 表示不动作电流 0.33A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录:

第 2 页 共 3 页

证书编号: CQC16001159721

纸号: 90406

LVR040(LVR040K、LVR040K-1,LVR040K-2,LVR040S,LVR040S-1,LVR040S-2)(电阻值范围 0.6Ω - 0.97Ω) :

040 表示不动作电流 0.40A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

LVR055(LVR055K,LVR055K-2,LVR055S,LVR055S-1,LVR055S-2) (电阻值范围 0.45Ω - 0.73Ω) :

055 表示不动作电流 0.55A; -1 表示拔脚; -2 表示卷装; K 表示标准弯脚引线; S 表示直引线;

LVR075(LVR075S,LVR075S-1,LVR075S-2,LVR075K,LVR075K-2,LVR075S-240,LVR075S-240-1,LVR075K-240,LVR075S-240-2,

LVR075K-240-2) (电阻值范围 0.316Ω - 0.483Ω) :

075 表示不动作电流 0.75A; -1 表示拔脚; -2 表示卷装; S 表示直引线; K 表示标准弯脚引线; -240 表示 240V

LVR100(LVR100S,LVR100S-2,LVR100S-240,LVR100S-240-2,LVR100K-240,LVR100K-240-2)(电阻值范围 0.218Ω - 0.334

Ω) : 100 表示不动作电流 1.0A; -2 表示卷装; S 表示直引线; K 表示标准弯脚引线; -240 表示 240V

LVR125(LVR125S,LVR125S-2,LVR125S-240,

LVR125S-240-2,LVR125K-240,LVR125K-240-2)(电阻值范围 0.165Ω - 0.253Ω) :

125 表示不动作电流 1.25A; -2 表示卷装; S 表示直引线; K 表示标准弯脚引线; -240 表示 240V

LVR200(LVR200S,

LVR200S-2,LVR200S-240,

LVR200S-240-2,LVR200K-240,LVR200K-240-2) (电阻值范围 0.089Ω - 0.131

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录:

第 3 页 共 3 页

证书编号: CQC16001159721

纸号: 90406

Ω):

200 表示不动作电流 2.0A; -2 表示卷装; S 表示直引线; K 表示标准弯脚引线; -240 表示 240V

气候类别 40/85/21.动作温度: 85°C, 额定电压: 120V/240VAC

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>