



IXYS
A Littelfuse Technology

Date:- 04 Oct, 2019

Data Sheet Issue:- P2

Tentative data

Insulated Gate Bi-Polar Transistor Type T1000EC33G

Absolute Maximum Ratings

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V _{CES}	Collector – emitter voltage	3300	V
V _{DC link}	Permanent DC voltage for 100 FIT failure rate.	1800	V
V _{GES}	Peak gate – emitter voltage	±20	V

	RATINGS	MAXIMUM LIMITS	UNITS
I _{C(DC)}	DC collector current, IGBT	1000	A
I _{CRM}	Repetitive peak collector current, t _p =1ms, IGBT	2000	A
I _{F(DC)}	Continuous DC forward current, Diode	1000	A
I _{FRM}	Repetitive peak forward current, t _p =1ms, Diode	2000	A
I _{FSM}	Peak non-repetitive surge t _p =10ms, V _{RM} =60%V _{RRM} , Diode (Note 4)	6000	A
I _{FSM2}	Peak non-repetitive surge t _p =10ms, V _{RM} ≤10V, Diode (Note 4)	6600	A
P _{MAX}	Maximum power dissipation, IGBT (Note 2)	6.4	kW
P _D	Maximum power dissipation, Diode (Note 2)	4.05	kW
(di/dt) _{cr}	Critical diode di/dt (note 3)	2000	A/μs
T _j	Operating temperature range.	-40 to +125	°C
T _{stg}	Storage temperature range.	-40 to +125	°C

Notes: -

- 1) Unless otherwise indicated T_j = 125°C.
- 2) T_{sink} = 25°C, double side cooled.
- 3) Maximum commutation loop inductance 200nH.
- 4) Half-sinewave, 125°C T_j initial.

Characteristics

IGBT Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
$V_{CE(sat)}$	Collector – emitter saturation voltage	-	2.57	2.97	$I_C = 1000A, V_{GE} = 15V, T_j = 25^\circ C$	V
		-	3.40	3.80	$I_C = 1000A, V_{GE} = 15V$	V
V_0	Threshold voltage	-	-	1.84	Current range: 333 – 1000A	V
r_s	Slope resistance	-	-	1.97		m Ω
$V_{GE(TH)}$	Gate threshold voltage	-	5.3	-	$V_{CE} = V_{GE}, I_C = 85mA$	V
I_{CES}	Collector – emitter cut-off current	-	10	25	$V_{CE} = V_{CES}, V_{GE} = 0V$	mA
I_{GES}	Gate leakage current	-	-	± 10	$V_{GE} = \pm 20V$	μA
C_{ies}	Input capacitance	-	135	-	$V_{CE} = 25V, V_{GE} = 0V, f = 1MHz$	nF
$t_{d(on)}$	Turn-on delay time	-	1.7	-	$I_C = 1000A, V_{CE} = 1800V, di/dt = 2000A/\mu s$	μs
$t_r(V)$	Rise time	-	1.8	-		μs
$Q_{g(on)}$	Turn-on gate charge	-	21	-	$V_{GE} = \pm 15V, L_s = 200nH$	μC
E_{on}	Turn-on energy	-	2.6	-	$R_{G(ON)} = 2.2\Omega, R_{G(OFF)} = 15\Omega, C_{GE} = 430nF$	J
$t_{d(off)}$	Turn-off delay time	-	5.3	-	Integral diode used as freewheel diode (Note 3, 4 & 5)	μs
$t_f(I)$	Fall time	-	1.5	-		μs
$Q_{g(off)}$	Turn-off gate charge	-	13	-		μC
E_{off}	Turn-off energy	-	2.7	-		J
I_{SC}	Short circuit current	-	3000	-	$V_{GE} = +15V, V_{CC} = 1800V, V_{CEmax} \leq V_{CES}, t_p \leq 10\mu s$	A

Diode Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
V_F	Forward voltage	-	2.66	2.95	$I_F = 1000A, T_j = 25^\circ C$	V
		-	3.0	3.3	$I_F = 1000A$	V
V_0	Threshold voltage	-	-	1.71	Current range 333 - 1000A	V
r_s	Slope resistance	-	-	1.59		m Ω
I_{rm}	Peak reverse recovery current	-	470	-	$I_F = 1000A, V_{GE} = \pm 15V, di/dt = 2000A/\mu s$	A
Q_{rr}	Recovered charge	-	1040	-		μC
t_{rr}	Reverse recovery time, 50% chord	-	1.7	-		μs
E_r	Reverse recovery energy	-	1.2	-		J

Thermal Characteristics

	PARAMETER	MIN	TYP	MAX	TEST CONDITIONS	UNITS
R_{thJK}	Thermal resistance junction to sink, IGBT	-	-	15.6	Double side cooled	K/kW
		-	-	25.4	Collector side cooled	K/kW
		-	-	40.5	Emitter side cooled	K/kW
R_{thJK}	Thermal resistance junction to sink, Diode	-	-	24.7	Double side cooled	K/kW
		-	-	37.9	Cathode side cooled	K/kW
		-	-	70.8	Anode side cooled	K/kW
F	Mounting force	25	-	35	Note 2	kN
W_t	Weight	-	1.2	-		kg

Notes:-

- 1) Unless otherwise indicated $T_j = 125^\circ C$.
- 2) Consult application note 2008AN01 for detailed mounting requirements
- 3) C_{GE} is additional gate – emitter capacitance added to output of gate drive
- 4) E_{on} integration time 15 μs from 10% rising I_C .
- 5) E_{off} integration time 15 μs from 90% falling V_{GE} .

Curves

Figure 1 – Typical collector-emitter saturation voltage characteristics




Figure 2 – Typical output characteristic




Figure 3 – Typical output characteristic




Figure 4 – Typical turn-on delay time vs gate resistance




Figure 5 – Typical turn-off delay time vs. gate resistance




Figure 6 – Typical turn-on energy vs. collector current




Figure 7 – Typical turn-on energy vs. di/dt




Figure 8 – Typical turn-off energy vs. collector current




Figure 9 – Turn-off energy vs voltage




Figure 10 – Safe operating area (IGBT)




Figure 11 – Typical diode forward characteristics




Figure 12 – Typical recovered charge




Figure 13 – Typical reverse recovery current




Figure 14 – Typical reverse recovery time




Figure 15 – Typical reverse recovery energy




Figure 16 – Safe operating area (Diode)




Figure 17 – Transient thermal impedance (IGBT)






Figure 18 – Transient thermal impedance (Diode)



Outline Drawing & Ordering Information



101A340

ORDERING INFORMATION

(Please quote 10 digit code as below)

T1000	EC	33	G
Fixed type Code	Fixed Outline Code	Voltage Grade $V_{CES}/100$ 33	Fixed format code

Typical order code: T1000EC33G ($V_{CES} = 3300V$)

IXYS Semiconductor GmbH
Edisonstraße 15
D-68623 Lampertheim
Tel: +49 6206 503-0
Fax: +49 6206 503-627
E-mail: marcom@ixys.de



IXYS
A Littelfuse Technology

IXYS UK Westcode Ltd
Langley Park Way, Langley Park,
Chippenham, Wiltshire, SN15 1GE.
Tel: +44 (0)1249 444524
E-mail: sales@ixysuk.com

IXYS Corporation
1590 Buckeye Drive
Milpitas CA 95035-7418
Tel: +1 (408) 457 9000
Fax: +1 (408) 496 0670
E-mail: sales@ixys.net

www.littelfuse.com

www.ixysuk.com

www.ixys.net

IXYS Long Beach
IXYS Long Beach, Inc.
2500 Mira Mar Ave, Long Beach
CA 90815
Tel: +1 (562) 296 6584
Fax: +1 (562) 296 6585
E-mail: service@ixyslongbeach.com

The information contained herein is confidential and is protected by Copyright. The information may not be used or disclosed except with the written permission of and in the manner permitted by the proprietors IXYS UK Westcode Ltd.

© IXYS UK Westcode Ltd.

In the interest of product improvement, IXYS UK Westcode Ltd reserves the right to change specifications at any time without prior notice.

Devices with a suffix code (2-letter, 3-letter or letter/digit/letter combination) added to their generic code are not necessarily subject to the conditions and limits contained in this report.

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics