

# MASM-14 14mm Close-Differential Reed Switch



## Description

The MASM-14 surface mount reed switch is a close-differential, sub-miniature, normally open switch with a 14mm long x 2.28mm diameter (0.551" x 0.090") glass envelope, capable of switching 200Vdc at 10W.

This reed switch is a surface mount version of MACD-14. It has high insulation resistance of  $10^{10}$  ohms minimum and a contact resistance of less than 100 milliohms. Both reed switches are intended for use in applications that require low hysteresis between Pull-In and Drop-Out values.


## Agency Approvals

| Agency | Agency File Number | Ampere-Turns Range |
|--------|--------------------|--------------------|
|        | E47258<br>E471070  | 10-30 AT           |

**Note:** Contact Littelfuse for specific agency approval ratings.

## Dimensions

Dimensions in mm (inch)



**Note:** Land pattern is Littelfuse recommendation only. User is responsible for proper PCB design.

## Features

- Surface mount normally open switch
- Capable of switching 200Vdc or 0.5A at up to 10W
- Low close/open hysteresis (close differential)

## Benefits

- Hermetically sealed switch contacts are not affected by and have no effect on their external environment
- Zero operating power required for contact closure
- Excellent for switching micro-controller logic level loads

## Applications

- Position Sensing
- Level Sensing
- Security
- Industrial Controls
- Office Equipment
- Home Appliances

## Switch Type

|              |   |
|--------------|---|
| Contact Form | A (SPST-NO)                                 |
| Materials    | Body: Glass<br>Leads: Tin-plated Ni-Fe wire |

**Note:** SPST-NO = Single-pole, single-throw, normally open

## Electrical Ratings

|                             |                                |                 |             |
|-----------------------------|--------------------------------|-----------------|-------------|
| Contact Rating <sup>1</sup> |                                | W/VA - max.     | 10          |
| Voltage <sup>3</sup>        | Switching <sup>2</sup>         | Vdc - max.      | 200         |
|                             |                                | Vac - max.      | 140         |
|                             | Breakdown <sup>4</sup>         | Vdc - min.      | 200         |
| Current <sup>3</sup>        | Switching <sup>2</sup>         | Adc - max.      | 0.50        |
|                             |                                | Aac - max.      | 0.35        |
|                             | Carry                          | Adc - max.      | 1.00        |
| Resistance                  | Contact, Initial Insulation    | $\Omega$ - max. | 0.100       |
|                             |                                | $\Omega$ - min. | $10^{10}$   |
| Capacitance                 | Contact                        | pF - typ.       | 0.3         |
| Temperature                 | Operating Storage <sup>5</sup> | $^{\circ}$ C    | -40 to +125 |
|                             |                                | $^{\circ}$ C    | -65 to +125 |

### Notes:

1. Contact rating - Product of the switching voltage and current should never exceed the wattage rating. Contact Littelfuse for additional load/life information.
2. When switching inductive and/or capacitive loads, the effects of transient voltages and/or currents should be considered. Refer to Application Notes AN108A and AN107 for details.
3. Electrical Load Life Expectancy - Contact Littelfuse with voltage, current values along with type of load.
4. Breakdown Voltage - per MIL-STD-202, Method 301.
5. Storage Temperature - Long time exposure at elevated temperature may degrade solderability of the leads.

# MASM-14 14mm Close-Differential Reed Switch


## Product Characteristics

| Operating Characteristics       |                    |                            |
|---------------------------------|--------------------|----------------------------|
| Operate Time <sup>1</sup>       |                    | 0.6ms - max.               |
| Release Time <sup>1</sup>       |                    | 0.2ms - max.               |
| Shock <sup>2</sup>              | 11ms 1/2 sine wave | 100G - max.                |
| Vibration <sup>2</sup>          | 50-2000 Hertz      | 30G - max.                 |
| Resonant Frequency              |                    | 5.3kHz typ                 |
| Magnetic Characteristics        |                    |                            |
| Pull-In Range <sup>3</sup>      | Ampere Turns       | 10-15, 15-20, 20-25, 25-30 |
| Rating Sensitivity <sup>4</sup> | Ampere Turns       | 20                         |
| Test Coil                       |                    | L4989                      |

**Notes:**

- Operate (including bounce)/Release Time - per EIA/NARM RS-421-A, diode suppressed coil (Coil II).
- Shock and Vibration - per EIA/NARM RS-421-A and MIL-STD-202.
- Pull-In Range - Contact Littelfuse for narrower AT ranges available. These AT ranges are the before modification AT of the MACD-14.
- Rating Sensitivity - The value at which contact ratings and operating characteristics are determined. Derating may be required below this value.


## Drop-Out vs. Pull-In Chart



**Note:**

Chart represents the range of Drop Out, min to max for a given Pull-In value of the MACD-14 prior to modification into the MASM-14.

## Part Numbering System




## Packaging

| Packaging Option | Packaging Specification | Quantity | Quantity & Packaging Code | Taping Width |
|------------------|-------------------------|----------|---------------------------|--------------|
| Tape and Reel    | EIA-RS-481-1            | 3000     | R                         | 32mm         |

# MASM-14 14mm Close-Differential Reed Switch

## TAPE DIMENSIONS mm (inch)



## REEL DIMENSIONS mm (inch)

