




RESISTANCE @ +25°C = 10,000 Ω $\pm$ 2%
 RESISTANCE/TEMPERATURE CURVE = "G"
 BETA " β " (0 TO +50°C) = 3,575°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.04%/°C NOMINAL
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 15 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 3 SECONDS MAXIMUM (STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	04/16/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com	
DRAWN BY	T. WILFONG		
DATE	04/22/97		
REV.	NONE		
LAYER	0 OF 1	NTC THERMISTOR	
		P/N DC103G9G	