


RESISTANCE @ +25°C = 10,000 Ω ± 1%
RESISTANCE/TEMPERATURE CURVE = "J"
BETA "β" (+25 TO +85°C) = 3,977°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −4.4%/°C NOMINAL
MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRE: 24 AWG, STRANDED CONDUCTOR,
TWO CONDUCTOR, PVC INSULATED ZIPCORD

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	01/11/12	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	© COPYRIGHT
DRAWN BY DAN DANKERT	U.S. SENSOR CORP.
DATE 01/11/12	714-639-1000 www.ussensor.com
REV. NONE	THERMISTOR PROBE
LAYER 0 OF 2	P/N USP12836