High Voltage Series

Littelfuse Circuit Protection 8mm 2Pole high voltage GDTs (ceramic gas discharge tubes), are commonly used to help protect high voltage circuits.

Littelfuse Circuit Protection high voltage GDTs offer a high level of surge protection, low capacitance and a broad array of break over voltage levels, making them suitable for applications such as branch circuits, medical electronics and surge protection on power lines. Littelfuse Circuit Protection GDTs can help equipment meet the most stringent regulatory standards.



Benefits:

- Helps provide overvoltage fault protection against high energy surges

Features:

- 2Pole, 8mm Axial and non Leaded devices
- Broad voltage range from 800-4000V
- Low capacitance
- Crowbar overvoltage protection
- UL 1449 recognized
- RoHS compliant
- Non-radioactive materials
- Capable up to 10kA 8/20 µs surge

Applications:

- Power Supplies
- Commercial Installations
- Medical Electronics
- Industrial Equipment and Machinery
- Appliance (Hi-Pot)

© 2016 Littelfuse, Inc
Specifications are subject to change without notice
Revised July 26, 2016

Document: SCD28143
Status: Released
Rev. A Date: JULY 26 1016


High Voltage Series

Device Voltage Ratings, Surge Rating, Capacitance, Insulation Resistance, UL


Part Description	DC Sparkover	Impulse Sparkover	Insulation Resistance	Capacitance	Impulse Discharge Current, 8/20us		AC Discharge Current, 50 Hz		UL Rating
	± 20% @100V/s (V)	100 V/µs (V)	500Vdc (MΩ)	1MHz (pF)	10 hits	1 hit	10 hits, 1S	1 hit, 9 cycles	UL1449 #E332226
GTCX28-801M-R05	800	1400	≥ 10,000	≤1	5kA	10kA	5A	N/A	All Devices
GTCX28-102M-R03	1000	1700	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-122M-R03	1200	1900	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-152L-R03	1500(±15%)	2200	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-212M-R03	2100	2700	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-242M-R03	2400	3300	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-252M-R03	2500	3500	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-272L-R03	2700 (±15%)	3700	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-302M-R03	3000	4000	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-312L-R03	3100 (±15%)	4300	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-362M-R03	3600	4600	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices
GTCX28-402M-R03	4000	5000	≥ 10,000	≤1	3KA	10kA	1A	5A	All Devices

Product Dimensions:

Axial Leads (GTCA28-XXXX-R0X)



No Leads (GTCN28-XXXX-R0X)



© 2016 Littelfuse, Inc
Specifications are subject to change without notice
Revised July 26, 2016

Document: SCD28143
Status: Released
Rev. A Date: JULY 26 1016

High Voltage Series

DIMENSIONS = MILLIMETERS [INCHES]

General Characteristics:

No Radioactive Materials

Storage temperature:	-40°C … +90°C
Operating temperature:	-40°C … +90°C
Electrode:	Fe-Ni alloy, Ni plated
Lead wire:	Tin Plated Copper

Materials Information

ROHS Compliant

Directive 2002/95/EC Compliant

ELV Compliant

Directive 2000/53/EC Compliant

Pb-Free

Packaging Information

Part Description	Tray / Reel	Standard Package
Axial Leads: GTCA28-XXXX-R0X	100	1000
No Leads: GTCN28-XXXM-R0X	100	2000

Part Numbering System

Example Part Number: GTCA28-212M-R03

GT =	Gas Tube
C =	Ceramic
A =	A= Axial Leads
2 =	2 Electrode device
8 =	8mm Diameter
212=	DC Spark Over Voltage of 2100V (at 100V/s)
M =	Tolerance of 20% on DC Spark Over Voltage
R =	Product Family Designator
03 =	Surge rating: 8x20Es 3kA 10 times

© 2016 Littelfuse,Inc
Specifications are subject to change without notice
Revised July 26, 2016

High Voltage Series

Part Marking Reference

Example Part Marking: XX 212 R03 HB

XX = Manufacturer' Mark
212 = Voltage Designator (212 = 2100V)
R03 = Product Family Designator - Surge Current 3kA (8x20µs 10 hits)
HB = Year and Week of Manufacture

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

© 2016 Littelfuse, Inc
Specifications are subject to change without notice
Revised July 26, 2016

Document: SCD28143
Status: Released
Rev. A Date: JULY 26 1016