SE-325 NEUTRAL-GROUNDING-RESISTOR MONITOR SETTING

Substation Identifcation: _____

Secondary Voltage: _____

SE-325 Model Number and Serial Number: _____

Ground-Fault Trip Level

CHECK ONE	GF SETTING
	4 A
	2 A
	0.5 A

Ground-Fault Trip Time

Setting: _____ seconds

Output Contact Mode of Operation

CHECK ONE	MODE SETTING
	SH (Shunt Trip)
	UV (Undervoltage Trip)

Sensing Resistor

CHECK ONE	MODEL
	ER-600VC
	ER-5KV
	ER-15KV
	ER-25KV
	ER-35KV

RES

CHECK ONE	NGR RESISTANCE
	100K
	20K

Remote Indication

CHECK ONE	MODEL
	None
	RK-13 Relay Interface Module
	RK-302 Remote Indication and Reset Kit
	RK-325 Remote Indication and Reset Assembly
	RK-325I Remote Indication Assembly

RES Trip Lvel (Vac)

For RES = 100K

Range is 100 to 2000 Vac

Setting: _____

For RES = 20K

Range is 20 to 400 Vac

Setting: _____

Current Transformer

CHECK ONE	CT SIZE
	CT200, 56 mm (2.2") Inner Diameter
	CT200L, 89 mm (3.5") Inner Diameter

NGR Ratings

Current: _____ A

Voltage: _____ V

© 2019 Littelfuse